

Digital Temperature Controllers

E5 D Series




The adjustments made by skilled workers are automated using Al. The innovation of production sites has begun.

Optimal and automatic temperature control without human intervention easily achieves both productivity and quality.

Previous temperature controllers have not only required a long time for start-up settings and variation adjustments, it has also been difficult to make the optimal adjustments without having experience and intuition. There were therefore some effects on quality. In response to this situation, OMRON developed the E5 D Series that includes "adaptive control technology." This makes it possible to detect the changes in the status which will have an effect on quality and to automatically control the temperature so that the optimal state is always

maintained, in the same way as a skilled worker would.

This frees production sites from troublesome start-up and adjustment work.




Causes of temperature variations on production lines

The answer was

the industry's first inclusion* of "adaptive control technology"

With the "adaptive control" incorporated into this product, the optimal PID value is calculated automatically for both the time of the start-up and for during stable production. Furthermore, it is possible to monitor the temperature control status of the machine to automatically adjust the PID value to obtain the optimal temperature control in response to changes such as workpiece changes and machine changes.




New value that supports advances in packaging machines

The sealing temperature is measured accurately and con maintain quality even at higher speeds.

Issues at production sites

- · Faster packaging to respond to the demand for foodstuffs arising due to the population increases in emerging nations
- · Increase in speed even when performing multiple-product production using a wide variety of packaging materials
- · At higher speeds, the temperature difference between the sealing surface and the control temperature widens, so the failure rate rises...



Packaging speed High speed


The E5 D Series Temperature Controllers solve the issues

The temperature of the sealing surface is stably controlled automatically with measurement of the sealing surface temperature and algorithms to suppress variations.

Even if the speed of the packaging process is increased, the difference between the sealing temperature and the

control temperature is minimized to perform stable automatic control, so it is possible to realize faster production while maintaining the product quality.

This also contributes to the use of thinner packaging materials and to high precision control.



Even in the production of multiple products, which hinders faster speeds because a change of packaging materials can mean that time is required to change the settings, the use of automatic control that has a small error in the sealing temperature enables a speedy response at production sites.


trolled automatically for packaging machines that can

Control performance that achieves new value

The temperature error is minimized with a temperature sensor for packaging machines* and an algorithm for packaging machines (automatic filter adjustment function) *Sold separately

"Temperature sensors for packaging machines" to measure the temperature of the sealing surface

The temperature of the heating bar surface is measured accurately and there is no effect from factors causing temperature variations, such as the speed of the packaging machine and changes to the packaging materials.




On a conventional machine, the temperature sensor was a little distance away from the sealing surface, so a difference occurred between the temperature of the sealing surface and the temperature that was actually being controlled. The temperature difference and failure rates increased in proportion to the packaging speed.


The installation position of the temperature sensor for packaging machines has been brought closer to the sealing surface to bring the temperature of the sensor closer to the temperature of the sealing surface. This minimizes the effects from variation in the surface temperature of the packaging materials.

"Automatic filter adjustment function" to suppress the instability in surface temperature measurements

By using the temperature sensor for packaging machines and the automatic filter adjustment function, it becomes possible to control the quality with the sealing temperature while also suppressing variation in the temperature with just a temperature controller, without relying on adjustments by workers.



When a temperature sensor for a packaging machines is used, there is sometimes periodic temperature variation generated when there is a marked effect from the heat on the packaging materials side.



When the automatic filter adjustment function of the E5 \Box D is used, this periodic temperature variation is suppressed automatically. It becomes possible to perform stable temperature control.

* Data measured by OMRON on a vertical flow packer.

New value that supports advances in molding machines

Stable control of the temperature changes arising from faster molding machines that can maximize production capacity.

Temperature variation

is approx. ±5°C.

Issues at production sites

- Increased productivity to respond to demand expansion related to infrastructure as a result of the economic development of the emerging nations and the transfer of production bases overseas.
- At higher speeds, adjustments by the workers become necessary to respond to temperature variations arising due to factors such as the materials compounding and cooling water...
- It is difficult to achieve high speed production while also maintaining the quality...

The E5 D Series Temperature Controllers solve the issues

Temperature variations due to speed changes and changes in the status of machines are suppressed without adjustments by the workers

Stable control is achieved automatically by detecting the temperature variations on the heat generating parts of the material that occur when the speed of the extrusion molding machine is increased and by detecting the temperature variations due to variation in the cooling water. The work required for setting are also greatly reduced.

Also saves energy on the machine

The stable control reduces the wasteful use of energy on the heater by up to 40% compared with conventional machines.

* Data measured by OMRON on a water-cooled twin screw extrusion molding machine.




OMRON | 7

speeds is performed automatically to realize

Control performance that achieves new value

Temperature variations are minimized with an algorithm for molding machines (water-cooling output adjustment function)

On a water-cooled extrusion molding machine, increased speed leads to temperature variations due to various causes and it was previously necessary for the workers to repeatedly make valve adjustments to stabilize the quality. With the E5 D, the water-cooling output adjustment function suppresses the temperature variations to a minimum and raises the production capacity with the quality maintained.



Causes of temperature variations


Nonlinear characteristics of water cooling In the type of cooling that uses the heat of evaporation, the cooling performance is nonlinear, so temperature variation occurs.

Variations in cooling water When there are variations in the cooling water system, temperature variations occur with the conventional auto-tuning because it is not possible to respond to changes in the status during operations.

"Water-cooling output adjustment function" to simultaneously suppress the causes of temperature variations and maintain stable performance


To Auto-tuning (Water cooling)

It is possible to suppress the temperature variations that occur due to the cooling output by using the auto-tuning (water cooling) before the materials are input to gain an understanding of the cooling characteristics.



Water-cooling output adjustment function

During the production after the materials have been input, the water-cooling output adjustment function constantly detects changes in the temperature and suppresses the temperature variation by automatically adjusting the proportional band (cooling).



* Data measured by OMRON on a water-cooled twin screw extrusion molding machine.

Main specifications

Temperature Controllers

Model	E5CD	ESED
Size (mm)	Front panel: 48×48 , Depth: 60	Front panel: 48 × 96, Depth: 60
Sensor input	All models: Thermocouple, platinum resistance thermometer, infrared temperature sensor (ES1B), or analog input (voltage/current); switchable.	
Indication accuracy (at the ambient temperature of 23°C)	Thermocouple: (±0.3% of indication value or ±1°C, whichever is greater) ±1 digit max. Platinum resistance thermometer: (±0.2% of indication value or ±0.8°C, whichever is greater) ±1 digit max. Analog input: ±0.2% FS ±1 digit max. CT input: ±5% FS ±1 digit max.	
Input sampling period	50 ms	
Control output	Relay output, voltage output (for driving SSR)	
Terminal type	M3 screw terminal block	
Approved standards	UL, KC, CE	

Model	E52-CA TAY ST
Туре	Lead wire type
Element type	К
Temperature range (Temperature range of sleeve)	0 to 650°C (0 to 260°C)
Protective tubing length (mm)	60/120
Protective tubing diameter (mm)	1 dia.
Compensating conductor	7 core/30 core
Temperature measuring junction	Grounded type

Temperature Sensors for Packaging Machines



Main functions of E5 D Series

- Automatic Filter Adjustment
- Water-cooling Output Adjustment

Resolution/accuracy

* Refer to the ESCD/ESED Digital Temperature Controllers and Temperature Sensors for Packaging Machines Datasheet (Cat. No. H223) for specification details.

OMRON Corporation **Industrial Automation Company** Kyoto, JAPAN Contact: www.ia.omron.com Regional Headquarters OMRON EUROPE B.V. **OMRON ELECTRONICS LLC** 2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31)2356-81-300/Fax: (31)2356-81-388 Tel: (1) 847-843-7900/Fax: (1) 847-843-7787 OMRON ASIA PACIFIC PTE. LTD.

No. 438A Alexandra Road # 05-05/08 (Lobby 2),

Tel: (65) 6835-3011/Fax: (65) 6835-2711

Alexandra Technopark,

Singapore 119967

OMRON (CHINA) CO., LTD. Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-5037-2222/Fax: (86) 21-5037-2200 Authorized Distributor:

© OMRON Corporation 2017 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice. CSM_1_1_0317 Cat. No. H222-E1-01